


1.Description

The 78Lxx series of fixed voltage monolithic integrated circuit voltage regulators are suitable for applications that required supply up to 150mA.


2.Features

- Maximum output current of 150mA
- Output voltage of 3.3V,5V,6V,8V,9V,10V, 12V,15V,18V and 24V
- Thermal overload protection
- Short circuit current limiting
- Output voltage accuracy: 1%

3.Pinning information




SOT-23



SOT-89

4.Block Diagram





5. Absolute Maximum Ratings

Characteristics	Symbol	Value	Units
Input voltage (for $V_O=3.3\sim18V$) (for $V_O=24V$)	V_I	35	V
		40	V
High power dissipation	P_D	800	mW
Junction Temperature Range	T_{OPR}	-40 to 105	°C
Storage Temperature Range	T_{STG}	-55 to 150	°C

6.1 Electrical Characteristics (78L33)

($V_I=5.3V$, $I_O=40mA$, $0<T_J<25^\circ C$, $C_1=0.33\mu F$, $C_O=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_O	$T_J=25^\circ C$	3.267	3.3	3.333	V
Load Regulation	ΔV_O	$T_J=25^\circ C$, $I_O=1mA\sim130mA$		10	60	mV
		$T_J=25^\circ C$, $I_O=1mA\sim70mA$		7	30	mV
Line regulation	ΔV_O	$5.3V\leq V_I\leq 20V$, $T_J=25^\circ C$		7	150	mV
		$6.3V\leq V_I\leq 20V$, $T_J=25^\circ C$		4	100	mV
Quiescent Current	I_q	$T_J=25^\circ C$		2	5.5	mA
Quiescent Current Change	ΔI_q	$6.3V\leq V_I\leq 20V$			1.5	mA
	ΔI_q	$1mA\leq I_O\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$, $T_J=25^\circ C$		40		μV
Temperature coefficient of V_O	$\Delta V_O/\Delta T$	$I_O=5mA$		0.45		mV/°C
Ripple Rejection	RR	$6.3V\leq V_I\leq 16.3V$, $f=120Hz$, $T_J=25^\circ C$	40	49		dB
Dropout Voltage	V_d	$T_J=25^\circ C$		1.7		V



6.2 Electrical Characteristics (78L05)

($V_i=10V$, $I_o=40mA$, $0<T_J<25^{\circ}C$, $C1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$T_J=25^{\circ}C$	4.95	5	5.05	V
Load Regulation	ΔV_o	$T_J=25^{\circ}C$, $I_o=1mA\sim 130mA$		11	60	mV
		$T_J=25^{\circ}C$, $I_o=1mA\sim 40mA$		5	30	mV
Line regulation	ΔV_o	$7V\leq V_i\leq 20V$, $T_J=25^{\circ}C$		8	150	mV
		$8V\leq V_i\leq 20V$, $T_J=25^{\circ}C$		6	100	mV
Quiescent Current	I_q			2	5.5	mA
Quiescent Current Change	ΔI_q	$8V\leq V_i\leq 20V$			1.5	mA
	ΔI_q	$1mA\leq V_i\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		40		μV
Temperature coefficient of V_o	$\Delta V_o / \Delta T$	$I_o=5mA$		0.65		mV/ $^{\circ}C$
Ripple Rejection	RR	$8V\leq V_i\leq 20V$, $f=120Hz$, $T_J=25^{\circ}C$	40	49		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V



6.3 Electrical Characteristics (78L06)

($V_i=12V$, $I_o=40mA$, $0<T_J<25^{\circ}C$, $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$T_J=25^{\circ}C$	5.94	6	6.06	V
Load Regulation	ΔV_o	$T_J=25^{\circ}C$, $I_o=1mA\sim 130mA$		12.8	80	mV
		$T_J=25^{\circ}C$, $I_o=1mA\sim 70mA$		5.8	40	mV
Line regulation	ΔV_o	$8.5V\leq V_i\leq 20V$, $T_J=25^{\circ}C$		64	175	mV
		$9V\leq V_i\leq 20V$, $T_J=25^{\circ}C$		54	125	mV
Quiescent Current	I_q			2	5.5	mA
Quiescent Current Change	ΔI_q	$9V\leq V_i\leq 20V$			1.5	mA
	ΔI_q	$1mA\leq V_i\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		49		μV
Temperature coefficient of V_o	$\Delta V_o / \Delta T$	$I_o=5mA$		0.75		$mV/^{\circ}C$
Ripple Rejection	RR	$10V\leq V_i\leq 20V$, $f=120Hz$, $T_J=25^{\circ}C$	38	46		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V



6.4 Electrical Characteristics (78L08)

($V_i=14V$, $I_o=40mA$, $0<T_J<25^{\circ}C$, $C1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$T_J=25^{\circ}C$	7.92	8	8.08	V
Load Regulation	ΔV_o	$T_J=25^{\circ}C$, $I_o=1mA\sim 130mA$		15	80	mV
		$T_J=25^{\circ}C$, $I_o=1mA\sim 70mA$		8	40	mV
Line regulation	ΔV_o	$10.5V\leq V_i\leq 23V$, $T_J=25^{\circ}C$		10	175	mV
		$11V\leq V_i\leq 23V$, $T_J=25^{\circ}C$		8	125	mV
Quiescent Current	I_q			2	5.5	mA
Quiescent Current Change	ΔI_q	$11V\leq V_i\leq 23V$			1.5	mA
	ΔI_q	$1mA\leq V_i\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		49		μV
Temperature coefficient of V_o	$\Delta V_o / \Delta T$	$I_o=5mA$		0.75		mV/ $^{\circ}C$
Ripple Rejection	RR	$11V\leq V_i\leq 23V$, $f=120Hz$, $T_J=25^{\circ}C$	36	45		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V



6.5 Electrical Characteristics (78L09)

($V_i=15V$, $I_o=40mA$, $0<T_J<25^{\circ}C$, $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$T_J=25^{\circ}C$	8.91	9	9.09	V
Load Regulation	ΔV_o	$T_J=25^{\circ}C$, $I_o=1mA\sim 130mA$		20	90	mV
		$T_J=25^{\circ}C$, $I_o=1mA\sim 40mA$		10	45	mV
Line regulation	ΔV_o	$11.5V\leq V_i\leq 24V$, $T_J=25^{\circ}C$		90	200	mV
		$13V\leq V_i\leq 24V$, $T_J=25^{\circ}C$		100	150	mV
Quiescent Current	I_q			2	5.5	mA
Quiescent Current Change	ΔI_q	$13V\leq V_i\leq 24V$			1.5	mA
	ΔI_q	$1mA\leq V_i\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		49		μV
Temperature coefficient of V_o	$\Delta V_o / \Delta T$	$I_o=5mA$		0.75		mV/ $^{\circ}C$
Ripple Rejection	RR	$12V\leq V_i\leq 23V$, $f=120Hz$, $T_J=25^{\circ}C$	36	44		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V



6.6 Electrical Characteristics (78L10)

($V_i=15V$, $I_o=40mA$, $0<T_J<25^{\circ}C$, $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$T_J=25^{\circ}C$	9.90	10	10.1	V
Load Regulation	ΔV_o	$T_J=25^{\circ}C$, $I_o=1mA\sim 130mA$		25	150	mV
		$T_J=25^{\circ}C$, $I_o=1mA\sim 40mA$		12	75	mV
Line regulation	ΔV_o	$12.5V\leq V_i\leq 27V$, $T_J=25^{\circ}C$		25	300	mV
		$14V\leq V_i\leq 27V$, $T_J=25^{\circ}C$		20	250	mV
Quiescent Current	I_q			2	5.5	mA
Quiescent Current Change	ΔI_q	$14V\leq V_i\leq 27V$			1.5	mA
	ΔI_q	$1mA\leq V_i\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		80		μV
Temperature coefficient of V_o	$\Delta V_o/\Delta T$	$I_o=5mA$		1		mV/ $^{\circ}C$
Ripple Rejection	RR	$13V\leq V_i\leq 25V$, $f=120Hz$, $T_J=25^{\circ}C$	36	42		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V



6.7 Electrical Characteristics (78L12)

($V_i=19V$, $I_o=40mA$, $0<T_J<25^{\circ}C$, $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$T_J=25^{\circ}C$	11.88	12	12.12	V
Load Regulation	ΔV_o	$T_J=25^{\circ}C$, $I_o=1mA\sim 130mA$		25	150	mV
		$T_J=25^{\circ}C$, $I_o=1mA\sim 40mA$		12	75	mV
Line regulation	ΔV_o	$14.5V\leq V_i\leq 27V$, $T_J=25^{\circ}C$		25	300	mV
		$16V\leq V_i\leq 27V$, $T_J=25^{\circ}C$		20	250	mV
Quiescent Current	I_q			2	5.5	mA
Quiescent Current Change	ΔI_q	$16V\leq V_i\leq 27V$			1.5	mA
	ΔI_q	$1mA\leq V_i\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		80		μV
Temperature coefficient of V_o	$\Delta V_o/\Delta T$	$I_o=5mA$		1		$mV/^{\circ}C$
Ripple Rejection	RR	$15V\leq V_i\leq 25V$, $f=120Hz$, $T_J=25^{\circ}C$	36	42		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V



6.8 Electrical Characteristics (78L15)

($V_I=23V$, $I_O=40mA$, $0<T_J<25^{\circ}C$, $C1=0.33\mu F$, $C_O=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_O	$T_J=25^{\circ}C$	14.85	15	15.15	V
Load Regulation	ΔV_O	$T_J=25^{\circ}C$, $I_O=1mA\sim 130mA$		20	150	mV
		$T_J=25^{\circ}C$, $I_O=1mA\sim 70mA$		25	150	mV
Line regulation	ΔV_O	$17.5V\leq V_I\leq 30V$, $T_J=25^{\circ}C$		25	150	mV
		$20V\leq V_I\leq 30V$, $T_J=25^{\circ}C$		15	75	mV
Quiescent Current	I_q			2.2	6	mA
Quiescent Current Change	ΔI_q	$20V\leq V_I\leq 30V$			1.5	mA
	ΔI_q	$1mA\leq V_I\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		90		μV
Temperature coefficient of V_O	$\Delta V_O/\Delta T$	$I_O=5mA$		1.3		$mV/^{\circ}C$
Ripple Rejection	RR	$18.5V\leq V_I\leq 28.5V$, $f=120Hz$, $T_J=25^{\circ}C$	33	39		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V



6.9 Electrical Characteristics (78L18)

($V_i=27V$, $I_o=40mA$, $0<T_J<25^{\circ}C$, $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$T_J=25^{\circ}C$	17.82	18	18.18	V
Load Regulation	ΔV_o	$T_J=25^{\circ}C$, $I_o=1mA\sim 130mA$		30	170	mV
		$T_J=25^{\circ}C$, $I_o=1mA\sim 40mA$		15	85	mV
Line regulation	ΔV_o	$21V\leq V_i\leq 33V$, $T_J=25^{\circ}C$		145	300	mV
		$22V\leq V_i\leq 33V$, $T_J=25^{\circ}C$		135	250	mV
Quiescent Current	I_q			2.2	6	mA
Quiescent Current Change	ΔI_q	$21V\leq V_i\leq 33V$			1.5	mA
	ΔI_q	$1mA\leq V_i\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		150		μV
Temperature coefficient of V_o	$\Delta V_o/\Delta T$	$I_o=5mA$		1.8		$mV/^{\circ}C$
Ripple Rejection	RR	$23V\leq V_i\leq 33V$, $f=120Hz$, $T_J=25^{\circ}C$	32	38		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V



6.10 Electrical Characteristics (78L24)

($V_i=33V$, $I_o=40mA$, $0<T_J<25^{\circ}C$, $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified) (Note 1)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Output Voltage	V_o	$T_J=25^{\circ}C$	23.76	24	24.24	V
Load Regulation	ΔV_o	$T_J=25^{\circ}C$, $I_o=1mA\sim 130mA$		40	200	mV
		$T_J=25^{\circ}C$, $I_o=1mA\sim 40mA$		20	100	mV
Line regulation	ΔV_o	$27V\leq V_i\leq 38V$, $T_J=25^{\circ}C$		160	300	mV
		$28V\leq V_i\leq 38V$, $T_J=25^{\circ}C$		150	250	mV
Quiescent Current	I_q			2.2	6	mA
Quiescent Current Change	ΔI_q	$21V\leq V_i\leq 38V$			1.5	mA
	ΔI_q	$1mA\leq V_i\leq 40mA$			0.1	mA
Output Noise Voltage	V_N	$10Hz\leq f\leq 100kHz$		200		μV
Temperature coefficient of V_o	$\Delta V_o/\Delta T$	$I_o=5mA$		2		$mV/^{\circ}C$
Ripple Rejection	RR	$27V\leq V_i\leq 38V$, $f=120Hz$, $T_J=25^{\circ}C$	30	37		dB
Dropout Voltage	V_d	$T_J=25^{\circ}C$		1.7		V

Notes


1: The Maximum steady state usable output current and input voltage are very dependent on the heating sinking and/or lead temperature length of the package. The data above represent pulse test conditions with junction temperatures as indicated at the initiation of test.

Note 2: Power dissipation $<0.75W$.

Note 3: Output voltage of 78Lxx.



7. Typical Application




Note 1: To specify an output voltage, substitute voltage value for "XX".

Note 2: Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators




8. Typical Characteristic





9.1 SOT-89 Package Outline Dimensions







DIMENSIONS (mm are the original dimensions)

Symbol	A	B	C	D	E	F	H	H1	L	L1	L2
Min	1.450	2.950	0.330	4.450	2.450	1.650	0.450	0.370	0.900	4.100	4.100
Max	1.550	3.050	0.430	4.550	2.550	1.750	0.580	0.480	1.000	4.300	4.350



9.2 SOT-23 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	L1	L2	C	D	E	E1	B	B1	θ
Min	0.900	0.020	0.300	0.300	0.100	2.800	1.200	2.300	1.800	0.950	0°
Max	1.100	0.100	0.500	0.500	0.120	3.000	1.400	2.500	2.000	TYP	8°



10.Ordering Information



Order Code	Marking	Package	Base QTY	Delivery Mode
UMW78L33-150	78L33	SOT-89	1000	Tape and reel
UMW 78L05-150	78L05	SOT-89	1000	Tape and reel
UMW 78L06-150	78L06	SOT-89	1000	Tape and reel
UMW 78L08-150	78L08	SOT-89	1000	Tape and reel
UMW 78L09-150	78L09	SOT-89	1000	Tape and reel
UMW 78L10-150	78L10	SOT-89	1000	Tape and reel
UMW78L12-150	78L12	SOT-89	1000	Tape and reel
UMW78L15-150	78L15	SOT-89	1000	Tape and reel
UMW78L18-150	78L18	SOT-89	1000	Tape and reel
UMW78L24-150	78L24	SOT-89	1000	Tape and reel
UMW 78L05S-150	L05	SOT-23	3000	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.