

36-V, 3.5-MHz, 15-V/μs Operational Amplifier, Automotive Qualification

Features

- Supply Voltage: 3 V to 36 V
- Low Supply Current: 1000 μA Maximum per Channel
- Differential Input Voltage Range to Supply Rail, can Work as Comparator
- Input Rail to -V_S, Rail-to-Rail Output
- Fast Response: 3.5-MHz Bandwidth, 15-V/μs Slew Rate, 100-ns Overload Recovery
- Low Offset Voltage:
 - ±2 mV Maximum at 25°C
 - ±4 mV Maximum at -40°C to 125°C
- Excellent EMIRR: 60 dB at 900 MHz
- Operating Temperature Range: -40°C to 125°C
- Qualified for Automotive Applications with AEC-Q100 Reliability Test

Description


The TP226x is a series of the newest high supply voltage amplifiers with low offset, low power, and stable high-frequency response. The TP226x series incorporates 3PEAK's proprietary and patented design techniques to achieve very good AC performance with a 3.5-MHz bandwidth, a 15-V/μs slew rate, and low distortion while drawing a quiescent current of only typical 700 μA per amplifier. The input common-mode voltage range extends to V₋, and the outputs swing rail-to-rail. The series can be used as plug-in replacements for many commercially available op-amps to reduce power and improve the input/output range and performance.

The combination of features makes the TP226x series an ideal choice for industrial control, motor control, portable audio amplification, sound ports, and other consumer audio.

Applications

- Motor Control
- Industrial Control
- Automotive

Typical Application Circuit



$$V_{OUT} = (I_{LOAD} \times R_{SHUNT}) \times (R_2 / R_1) + V_{REF}$$

$$\text{When } R_3 = R_1, R_2 = R_4, R_{SHUNT} \ll R_1$$

Table of Contents

Features	1
Applications	1
Description	1
Typical Application Circuit	1
Revision History	3
Pin Configuration and Functions	4
Specifications	6
Absolute Maximum Ratings ⁽¹⁾	6
ESD, Electrostatic Discharge Protection.....	6
Thermal Information.....	6
Electrical Characteristics.....	7
Typical Performance Characteristics.....	10
Tape and Reel Information	15
Package Outline Dimensions	16
SOT23-5.....	16
SOP8.....	17
SOP14.....	18
TSSOP14.....	19
Order Information	20
IMPORTANT NOTICE AND DISCLAIMER	21

Revision History

Date	Revision	Notes
	Rev.A.0	Initial version.
2025-02-20	Rev.A.1	The following updates are all about the new datasheet formats or typos, and the actual product remains unchanged. • Updated to a new datasheet format. • Added part number: TP2264-TS2R-S.

Pin Configuration and Functions




Table 1. Pin Functions: TP2261

Pin No.	Name	I/O	Description
1	Out	O	Output
2	-Vs		Negative power supply
3	+In	I	Non-inverting input
4	-In	I	Inverting input
5	+Vs		Positive power supply

36-V, 3.5-MHz, 15-V/μs Operational Amplifier, Automotive Qualification




Table 2. Pin Functions: TP2262, TP2264

Pin No.		Name	I/O	Description
TP2262	TP2264			
SOP8	SOP14/ TSSOP14			
1	1	Out A	O	Output
2	2	-In A	I	Inverting input
3	3	+In A	I	Non-inverting input
4	11	-Vs		Negative power supply
5	5	+In B	I	Non-inverting input
6	6	-In B	I	Inverting input
7	7	Out B	O	Output
8	4	+Vs		Positive power supply
	8	Out C	O	Output
	9	-In C	I	Inverting input
	10	+In C	I	Non-inverting input
	12	+In D	I	Non-inverting input
	13	-In D	I	Inverting input
	14	Out D	O	Output

36-V, 3.5-MHz, 15-V/ μ s Operational Amplifier, Automotive Qualification

Specifications

Absolute Maximum Ratings ⁽¹⁾

Parameter		Min	Max	Unit
	Supply Voltage, (+V _S) – (–V _S)		40	V
	Input Voltage	(–V _S) – 0.3	(+V _S) + 0.3	V
	Differential Input Voltage		(+V _S) – (–V _S)	V
	Input Current: +IN, –IN ⁽²⁾	–10	10	mA
	Output Short-Circuit Duration ⁽³⁾		Infinite	
T _J	Maximum Junction Temperature		150	°C
T _A	Operating Temperature Range	–40	125	°C
T _{STG}	Storage Temperature Range	–65	150	°C
T _L	Lead Temperature (Soldering, 10 sec)		260	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. Exposure to any Absolute Maximum Rating condition for extended periods may affect device reliability and lifetime.

(2) The inputs are protected by ESD protection diodes to each power supply. If the input extends more than 300 mV beyond the power supply, the input current should be limited to less than 10 mA.

(3) A heat sink may be required to keep the junction temperature below the absolute maximum. This depends on the power supply voltage and how many amplifiers are shorted. The thermal resistance varies with the amount of PC board metal connected to the package. The specified values are for short traces connected to the leads.

ESD, Electrostatic Discharge Protection

Symbol	Parameter	Condition	Minimum Level	Unit
HBM	Human Body Model ESD	AEC-Q100-002	2	kV
CDM	Charged Device Model ESD	AEC-Q100-011	1	kV

Thermal Information

Package Type	θ_{JA}	θ_{JC}	Unit
SOT23-5	250	81	°C/W
SOP8	158	43	°C/W
SOP14	120	36	°C/W
TSSOP14	108	43	°C/W

36-V, 3.5-MHz, 15-V/ μ s Operational Amplifier, Automotive Qualification

Electrical Characteristics

All test conditions: $V_S = (+V_S) - (-V_S) = 30\text{ V}$, $T_A = 25^\circ\text{C}$, $R_L = 10\text{ k}\Omega$ to $V_S / 2$, unless otherwise noted.

Symbol	Parameter	Conditions	T _A	Min	Typ	Max	Unit
Power Supply							
V _S	Supply Voltage Range			3		36	V
I _Q	Quiescent Current per Amplifier	V _S = 30 V, TP2261			1000	1500	μA
			−40°C to 125°C			2500	μA
		V _S = 5 V, TP2261			850	1300	μA
			−40°C to 125°C			2000	μA
		V _S = 30 V, TP2262/2264			700	1000	μA
			−40°C to 125°C			2000	uA
		V _S = 5 V, TP2262/2264			600	850	μA
			−40°C to 125°C			1500	μA
PSRR	Power Supply Rejection Ratio	V _S = 3 V to 36 V		95	120		dB
			−40°C to 125°C	80			dB
Input Characteristics							
V _{OS}	Input Offset Voltage	V _S = 30 V, V _{CM} = 0 V to 28 V		−2	0.1	2	mV
			−40°C to 125°C	−4		4	mV
		V _S = 30 V, V _{CM} = 28.5 V		−3		3	mV
			−40°C to 125°C	−5		5	mV
		V _S = 5 V, V _{CM} = 2.5 V		−2	0.1	2	mV
			−40°C to 125°C	−4		4	mV
V _{OS} TC	Input Offset Voltage Drift		−40°C to 125°C		2		μV/°C
I _B	Input Bias Current			−250	25	250	pA
			−40°C to 125°C		1	10	nA
I _{OS}	Input Offset Current ⁽¹⁾			−250	25	250	pA
			−40°C to 125°C		1	10	nA
I _{IN}	Differential Input Current	V _S = 36 V, V _{ID} = 36 V			10		nA

36-V, 3.5-MHz, 15-V/ μ s Operational Amplifier, Automotive Qualification

Symbol	Parameter	Conditions	T _A	Min	Typ	Max	Unit
			−40°C to 125°C		100		nA
C _{IN}	Input Capacitance	Differential mode			5		pF
		Common mode			5		pF
A _v	Open-Loop Voltage Gain			105	120		dB
			−40°C to 125°C	90			dB
V _{CMR}	Common-Mode Input Voltage Range			(V−)		(V+) − 1.5	V
CMRR	Common-Mode Rejection Ratio	V _{CM} = 0 V to 28 V		105	130		dB
			−40°C to 125°C	90			dB
Output Characteristics							
V _{OH}	Output Swing from Positive Rail	R _{LOAD} = 10 kΩ to V _S / 2			200	300	mV
			−40°C to 125°C			600	mV
		R _{LOAD} = 2 kΩ to V _S / 2			1.1	1.4	V
			−40°C to 125°C			2.8	V
V _{OL}	Output Swing from Negative Rail	R _{LOAD} = 10 kΩ to V _S / 2			200	300	mV
			−40°C to 125°C			600	mV
		R _{LOAD} = 2 kΩ to V _S / 2			0.8	1	V
			−40°C to 125°C			2	V
I _{SC}	Output Short-Circuit Current			25	32		mA
		−40°C to 125°C		10			mA
AC Specifications							
GBW	Gain-Bandwidth Product				3.5		MHz
SR	Slew Rate	G = 1, 10-V step			15		V/μs
		Open loop		9	15		V/μs
			−40°C to 125°C	6			V/μs
t _{OR}	Overload Recovery				100		ns
t _s	Settling Time, 0.1%	G = −1, 10-V step			0.8		μs
	Settling Time, 0.01%				1		μs
PM	Phase Margin	V _S = 36 V, R _L = 10 kΩ, C _L = 100 pF			60		°

36-V, 3.5-MHz, 15-V/ μ s Operational Amplifier, Automotive Qualification

Symbol	Parameter	Conditions	T _A	Min	Typ	Max	Unit
GM	Gain Margin	V _S = 36 V, R _L = 10 k Ω , C _L = 100 pF			15		dB
Noise Performance							
E _N	Input Voltage Noise	f = 0.1 Hz to 10 Hz			1.7		μ V _{RMS}
e _N	Input Voltage Noise Density	f = 1 kHz			30		nV/ $\sqrt{\text{Hz}}$
i _N	Input Current Noise	f = 1 kHz			2		fA/ $\sqrt{\text{Hz}}$
THD+N	Total Harmonic Distortion and Noise	f = 1 kHz, G = 1, R _L = 10 k Ω , V _{OUT} = 6 V _{RMS}			0.0005		%

(1) Provided by the bench tests and design simulation.

Typical Performance Characteristics

All test conditions: $V_S = \pm 15\text{ V}$, $V_{CM} = 0\text{ V}$, $R_L = 10\text{ k}\Omega$, unless otherwise noted.




Figure 1. Quiescent Current vs. Supply Voltage, 2-Channel, TP2262




Figure 2. Quiescent Current vs. Temperature, 2-Channel, TP2262




Figure 3. Offset Voltage vs. Common-Mode Voltage




Figure 4. Offset Voltage vs. Common-Mode Voltage




Figure 5. V_{OS} vs. Temperature




Figure 6. V_{OS} vs. Temperature

36-V, 3.5-MHz, 15-V/ μ s Operational Amplifier, Automotive Qualification




Figure 7. Input Current in Large Vdm vs. Temperature




Figure 8. I_B vs. Temperature




Figure 9. PSRR vs. Frequency




Figure 10. CMRR vs. Frequency




Figure 11. PSRR vs. Temperature




Figure 12. CMRR vs. Temperature

36-V, 3.5-MHz, 15-V/ μ s Operational Amplifier, Automotive Qualification




Figure 13. EMIRR IN+ vs. Frequency




Figure 14. Open-Loop Gain and Phase vs. Frequency





Figure 15. Close-Loop Gain and Phase vs. Frequency



$V_S = \pm 1.5$ V, $V_{IN} = 100$ mV_{PP}, $R_L = 10$ K, $C_L = 100$ pF, $G = 1$

Figure 16. Waveform under 3-V Supply Voltage




Figure 17. Maximum Peak Output Voltage vs. Load Resistance








Figure 18. Maximum Peak Output Voltage vs. Load Resistance

36-V, 3.5-MHz, 15-V/ μ s Operational Amplifier, Automotive Qualification


Figure 19. Positive Output Voltage vs. Output Current

Figure 20. Negative Output Voltage vs. Output Current

Figure 21. Positive Output Voltage vs. Output Current

Figure 22. Negative Output Voltage vs. Output Current


Voltage: 1 V/div, Time: 200 ns/div
 $V_S = 5\text{ V}$, $V_{IN} = 2\text{ V}$, $R_L = \text{Open}$, $G = 3$

Figure 23. Positive Overload Recovery


Voltage: 1 V/div, Time: 200 ns/div
 $V_S = 5\text{ V}$, $V_{IN} = 2\text{ V}$, $R_L = \text{Open}$, $G = 3$

Figure 24. Negative Overload Recovery

36-V, 3.5-MHz, 15-V/ μ s Operational Amplifier, Automotive Qualification



Voltage: 20 mV/div, Time: 100 ns/div

$V_S = \pm 15$ V, $R_L = 2$ K, $C_L = 100$ pF, $G = 1$


Figure 25. 100-mV Signal Step Response



Voltage: 2 V/div, Time: 1 μ s/div


$V_S = \pm 15$ V, $R_L = 2$ K, $C_L = 100$ pF, $G = 1$

Figure 26. 10-V Signal Step Response




$V_S = \pm 15$ V, $V_{CM} = 0$ V

Figure 27. Voltage Noise Spectral Density vs. Frequency



$V_S = \pm 15$ V, $V_{CM} = 0$ V, $G = 1$


Figure 28. THD+N vs. Frequency



$V_S = \pm 15$ V, $V_{CM} = 0$ V

Figure 29. Crosstalk vs. Frequency

Tape and Reel Information



Order Number	Package	D1 (mm)	W1 (mm)	A0 (mm) ⁽¹⁾	B0 (mm) ⁽¹⁾	K0 (mm) ⁽¹⁾	P0 (mm)	W0 (mm)	Pin1 Quadrant
TP2261L1-S5TR-S	SOT23-5	179.0	12.0	3.3	3.25	1.4	4.0	8.0	Q3
TP2262L1-SO1R-S	SOP8	330.0	17.6	6.5	5.4	2.0	8.0	12.0	Q1
TP2264L1-SO2R-S	SOP14	330.0	21.6	6.5	9.1	1.8	8.0	16.0	Q1
TP2264-TS2R-S	TSSOP14	330.0	17.6	6.8	5.5	1.5	8.0	12.0	Q1





(1) The value is for reference only. Contact the 3PEAK factory for more information.

Package Outline Dimensions

SOT23-5

Package Outline Dimensions


S5T(SOT23-5-A)



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	MIN	MAX	MIN	MAX
A	1.050	1.250	0.041	0.049
A1	0.000	0.150	0.000	0.006
A2	1.000	1.200	0.039	0.047
b	0.280	0.500	0.011	0.020
c	0.100	0.230	0.004	0.009
D	2.820	3.020	0.111	0.119
E	2.600	3.000	0.102	0.118
E1	1.500	1.720	0.059	0.068
e	0.950 BSC		0.037 BSC	
L	0.300	0.600	0.012	0.024
θ	0	8°	0	8°

NOTES




1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

SOP8
Package Outline Dimensions
SO1(SOP-8-A)


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	MIN	MAX	MIN	MAX
A	1.350	1.750	0.053	0.069
A1	0.050	0.250	0.002	0.010
A2	1.250	1.550	0.049	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.007	0.010
D	4.700	5.100	0.185	0.201
E	5.800	6.200	0.228	0.244
E1	3.800	4.000	0.150	0.157
e	1.270 BSC		0.050 BSC	
L	0.400	1.000	0.016	0.039
θ	0	8°	0	8°

NOTES




1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

SOP14
Package Outline Dimensions
SO2(SOP-14-A)


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	MIN	MAX	MIN	MAX
A	1.350	1.750	0.053	0.069
A1	0.050	0.250	0.002	0.010
A2	1.250	1.650	0.049	0.065
b	0.310	0.510	0.012	0.020
c	0.100	0.250	0.004	0.010
D	8.450	8.850	0.333	0.348
E	5.800	6.200	0.228	0.244
E1	3.800	4.000	0.150	0.157
e	1.270 BSC		0.050 BSC	
L	0.400	1.270	0.016	0.050
θ	0	8°	0	8°

NOTES

1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

TSSOP14
Package Outline Dimensions
TS2(TSSOP-14-A)


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	MIN	MAX	MIN	MAX
A	0.900	1.200	0.035	0.047
A1	0.050	0.150	0.002	0.006
A2	0.800	1.050	0.031	0.041
b	0.190	0.300	0.007	0.012
c	0.090	0.200	0.004	0.008
D	4.900	5.100	0.193	0.201
E	6.200	6.600	0.244	0.260
E1	4.300	4.500	0.169	0.177
e	0.650 BSC		0.026 BSC	
L	0.450	0.750	0.018	0.030
θ	0	8°	0	8°

NOTES

1. Do not include mold flash or protrusion.
2. This drawing is subject to change without notice.

Order Information

Order Number	Operating Temperature Range	Package	Marking Information	MSL	Transport Media, Quantity	Eco Plan
TP2261L1-S5TR-S	-40 to 125°C	SOT23-5	226	3	Tape and Reel, 3000	Green
TP2262L1-SO1R-S	-40 to 125°C	SOP8	TP2262	1	Tape and Reel, 4000	Green
TP2264L1-SO2R-S ⁽¹⁾	-40 to 125°C	SOP14	TP2264		Tape and Reel, 2500	Green
TP2264-TS2R-S	-40 to 125°C	TSSOP14	2264	3	Tape and Reel, 3000	Green

(1) For future products, contact the 3PEAK factory for more information and samples.

Green: 3PEAK defines "Green" to mean RoHS compatible and free of halogen substances.

IMPORTANT NOTICE AND DISCLAIMER

Copyright© 3PEAK 2012-2025. All rights reserved.

Trademarks. Any of the 思瑞浦 or 3PEAK trade names, trademarks, graphic marks, and domain names contained in this document /material are the property of 3PEAK. You may NOT reproduce, modify, publish, transmit or distribute any Trademark without the prior written consent of 3PEAK.

Performance Information. Performance tests or performance range contained in this document/material are either results of design simulation or actual tests conducted under designated testing environment. Any variation in testing environment or simulation environment, including but not limited to testing method, testing process or testing temperature, may affect actual performance of the product.

Disclaimer. 3PEAK provides technical and reliability data (including data sheets), design resources (including reference designs), application or other design recommendations, networking tools, security information and other resources "As Is". 3PEAK makes no warranty as to the absence of defects, and makes no warranties of any kind, express or implied, including without limitation, implied warranties as to merchantability, fitness for a particular purpose or non-infringement of any third-party's intellectual property rights. Unless otherwise specified in writing, products supplied by 3PEAK are not designed to be used in any life-threatening scenarios, including critical medical applications, automotive safety-critical systems, aviation, aerospace, or any situations where failure could result in bodily harm, loss of life, or significant property damage. 3PEAK disclaims all liability for any such unauthorized use.

This page intentionally left blank